

Anwendungsbeispiele für das JA-Baukastensystem

Examples for using the JA-Modular System



Im JA-Baukastensystem enthalten:

- 1 Stck. Schutzgaseintritt
- 1 Stck. Schutzgasaustritt
- 2 Stck. Silikon Dichtscheibe
- 2 Stck. Mutter
- 1 Stck. VA-Schutzgas-Diffusor
- 2 Stck. Biegbarer Gliederarm
- 1 Stck. Starre Verbindung 50 mm lg. SW14
- 1 Stck. Starre Verbindung 60 mm lg. SW14
- 1 Stck. Sintermetall Gasaustritt
- 1 Stck. Kettenglied schraubbar
- 1 Stck. VA Zugseil 10mxØ2mm
- 1 Stck. PVC Schlauch 10m x Ø5mm/Ø8mm
- 4 Stck. VA Schlauchschellen
- 1 Stck. Schlauch Kupplung
- 1 Stck. Schlauch Tülle
- 1 Stck. Flaschenanschluss mit Mutter ¼" Rechts

Content of a complete JA-Modular System unit:

- 1 piece of protective gas inlet
- 1 piece of protective gas outlet
- 2 pieces of heat-resistant sealing discs
- 2 pieces of nuts
- 1 piece of protective gas diffuser, stainless steel
- 2 piece of flexible arm
- 1 piece of rigid pipe 50 mm long, SW 14
- 1 piece of rigid pipe 60 mm long, SW 14
- 1 piece of dry powdered protective gas outlet
- 1 piece of hookØ4mm
- 1 piece of 10 m stainless steel release cableØ2mm
- 1 piece of 10 m two-ply PVC hoseØ5x8mm
- 4 pieces of stainless steel hose clips with insert ring Ø 9,5 mm
- 1 piece of complete coupling DN 5 (brass) for coupling
- 1 piece of mouthpiece for hose, DN 5 (brass) for coupling
- 1 piece of nut G ¼" R with mouthpiece DN 5 (brass), suitable for Argon pressure reducer